




"Make Life Safer"



## UV-V and Ozone Germicidal Table Light (NLUVCH150-1OZ)

### TECHNICAL FEATURES

Lamp Model	NLUVCH150-1OZ
Lamp power Watt	150w
UV wavelength	UV-V 185nm Ozone
Static area applicable	up to 110m <sup>2</sup>
Ozone flow generated (g/hour)	N/A
Disinfection cap. (m <sup>3</sup> /h) in millijoules/cm <sup>2</sup> (30mj/cm <sup>2</sup> )	N/A
Auxiliary control devices (timer and timer time, human presence sensor, ignition delay and ignition delay time)	30s delay switch 15-30-60 mins timer time
Arm adjustment angle in degrees °	N/A - 360° disinfection
Supply voltage in volts	AC 220-240V
Absorption in Ampere	0,73A
Estimated tube life	>8000Hrs
Type of tube	Clear Quartz glass tube
Lamp dimensions	Ø190xH900mm
Packaging dimensions	N/A
Lamp weight	1,55Kg
Weight with packaging	2,55Kg
Frame construction material and screws	Iron black finishing and AL base
Operating temperature	-20° C <--> 45° C
IP dust and humidity protection degree	IP20

Disinfection with ultraviolet rays is an effective way to destroy microorganisms including bacteria, viruses, mold spores, acting on the DNA-RNA of microorganisms by irradiating with the appropriate wavelength of ultraviolet rays UV-C at 253.7nm or UV- V at 185nm with generation of Ozone gas leads to the death of the cell, after a correct exposure to rays and gases, a mortality level of virus bacteria and spores exceeds 99.9%.

These destroy the DNA molecular bonds of microorganisms, producing thymine dimers in their DNA and destroying them, rendering them harmless or impeding their growth and reproduction.

The ignition times are variable depending on the power of the lamp compared to the surface to be irradiated. The dosage is measured in microwatts per second per square centimeter:  $\mu\text{W} / \text{cm}^2$ . Dosages from 2 to 8  $\mu\text{W} / \text{cm}^2$  kill 99.9% of spore virus bacteria.

When the lamp is turned on in the room, there must be no human presence, animals and plants, the sterilization cycles normally last 15-30-60 minutes or more for large rooms greater than 150 m<sup>2</sup>, the cycles are regulated by a timer or by a remote control depending on the model.

